

Ball joint DN 90

Oper. pressure [bar]: 10

Oper. temp. range [K]: 20 ÷ 360

Oper. travel ranges (max.)
- angular [°] : ± 6

Weight (max) [Kg] : 3.4

Spring rates (max.)
- angular [N m/°] : < 3

Operating fluids : GHe – GN2

Bellows material : 316L

Application : A5 EPC press. lines

Status : Developed prototype

