

## SERIES 71

### GREY NON-MARKING THERMOPLASTIC RUBBER WHEELS WITH POLYPROPYLENE CENTRE



#### Wheel description

Grey non-marking thermoplastic rubber tread, hardness 85+/-4 Shore A. Polypropylene centre.

#### Hub

The hub is available with plain bearing, with roller bearing, with stainless steel roller bearing.

**Diameters:** 80-200 mm

**Carrying capacities:** 70-225 daN

### Fittings with swivel, fixed and swivel with brake brackets



#### Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm

Models available: with top plate fastening, with bolt hole

Suitable brakes: front-locking and central (hexagonal) brake systems

### Uses

#### Environments

Suitable for use in humid environments with medium-hars chemical; not suitable for applications where organic solvents, chlorinated substances, hydrocarbons and mineral oils are present.

Usage temperatures: from -20 °C to +70 °C

#### Floors



#### Handling

