

SERIES 74

VULKOLLAN[®] TRANSPALLET ROLLERS, STEEL CENTRE



Roller description

Vulkollan[®] transpallet roller, hardness 93 +/- 2 Shore A, excellent rolling resistance and elasticity, good resistance to wear and to tearing. Weldless steel centre.

Hub

The housing is obtained by moulding and turning and contains ball bearings series Z. The hub is available also without bearings.

Diameters: 80-85 mm

Carrying capacities: 650-1000 daN

Uses

Environments

The series is suitable for use in industrial environments for carrying medium-heavy loads, including with mixed outdoor-indoor use. Can be used at speeds of up to 16 km/h; possibility of using for mechanised towing.

Usage temperatures: from -20 °C to +80 °C

Floors



Handling

