

SERIES 78

INJECTION POLYURETHANE TRANSPALLET ROLLERS, POLYAMIDE 6 CENTRE



Roller description

"TR" polyurethane transpallet roller, hardness 95 +/- 3 Shore A, excellent rolling resistance and elasticity, good resistance to wear and to tearing. Polyamide 6 centre.

Hub

The housing is obtained by moulding and turning and contains ball bearings series Z. The hub is available also without bearings

Diameters: 82-85 mm

Carrying capacities: 450-600 daN

Uses

Environments

Suitable for environments where atmospheric agents, alcohol, glycol, mineral and organic acids, base solutions and saturated vapours are present.

Usage temperatures: from -15 °C to +80 °C

Floors



Handling

