

SERIES 63

VULKOLLAN® WHEELS, FORGED STEEL CENTRE



Wheel description

Vulkollan® polyurethane tread; hardness 93 +/-2 Shore A. Forged steel centre. Suitable for environment with atmospheric agents, alcohol and glycol.

Hub

The housing is obtained by moulding and turning and contains ball bearings series Z. The hub is available also without bearings.

Diameters: 100-250 mm

Carrying capacity: 250-1500 daN

Fittings with swivel, fixed and swivel with brake brackets



Standard duty brackets type NL

Max. carrying capacity 400 daN – available diameters 80-300 mm
Top plate fastening.
Front-locking brake systems.



Medium duty brackets type M

Max. carrying capacity 500 daN – available diameters 150-200 mm
Top plate fastening.
Adjustable front-locking brake



Medium-heavy duty brackets type P

Max. carrying capacity 750 daN – available diameters 80-200 mm
Top plate fastening.
Front-locking and adjustable rear-locking brake systems



Extra-heavy duty brackets type EP

Max. carrying capacity 1600 daN – available diameters 100-250 mm
Top plate fastening. Adjustable rear-locking brake systems

Uses

Environments

Suitable for environment with atmospheric agents, alcohol and glycol; not suitable for applications where mineral and organic acids, base solutions and saturated vapour are present.

Usage temperatures: from -20 °C to +80 °C

Floors



Handling

